

Your light o<sup>~</sup> ers 2 colors of light output to suit any mood.

To select "White" light output, rotate the bezel 30 degrees counter clockwise until the ÿrst detent is acheived.

To dim the "White" light output, rotate the bezel an additional 10 degrees counter clockwise and hold until the desired intensity is acheived then release the bezel.

To select the second color and dim, follow the exact instructions above, only start by rotating the bezel clockwise.

Light circuits should be protected with an appropriately sized fuse. Each light draws approximately 290mA at 12VDC and 160mA at 24VDC. Fuses on circuits with multiple lights should be sized accordingly.